


CARTRIDGE

308 Norma Magnum - 175/180 grain

Version 8.0

Nosler®

UP FRONT



308 Norma Magnum - 175/180 grain

30 Cal. (.30)

MAXIMUM O.A.C.L. 3.347"

B.C. S.D.

Custom Competition®	175gr. HPBT	0.505	0.264
AccuBond®	180gr. Spitzer	0.507	0.271
Ballistic Tip®	180gr. Spitzer	0.507	0.271
CT® Ballistic Silvertip®	180gr. Spitzer	0.507	0.271
E-Tip®	180gr. Spitzer	0.523	0.271
Due to internal construction differences, always begin with starting loads when using E-Tip® products.			
Partition®	180gr. PPT	0.361	0.271
Partition®	180gr. Spitzer	0.474	0.271

CASE TYPE:	Norma	PRIMER TYPE	Fed 215
CASE HOLDS:	69.4 Gr. WATER	BARREL Length/Make	24" Wiseman
		BARREL Twist	1-10"

POWDER TYPE	POWDER CHG. GRS.	MUZZLE VEL. F.P.S.	LOAD DENSITY (VOLUME)
IMR 7828 Most Accurate Powder Tested	72.5 MAX.	2860	** 111%
	70.5	2770	** 108%
	68.5 *	2680	** 105%
IMR 4350	68.0 MAX.	2900	** 104%
	66.0	2820	** 101%
	64.0 *	2740	98%
Viht N160	67.0 MAX.	2906	** 107%
	65.0	2830	** 104%
	63.0 *	2753	** 101%
IMR 4895	58.0 MAX.	2932	92%
	56.0	2787	89%
	54.0 *	2642	86%
RL19	69.0 * MAX.	2956	** 108%
	67.0	2865	** 105%
	65.0	2774	** 102%
IMR 4831	71.0 * MAX.	2980	** 109%
	69.0	2880	** 106%
	67.0	2780	** 103%

All cartridge measurements are SAAMI maximum and due to variations from manufacturers actual measurements may vary

* Because Nosler, Inc. has no control over the actual components selected, the manner in which they are assembled or the condition of the firearm used, no responsibility, either expressed or implied is assumed for the use of this data.

In no event shall Nosler, Inc. be liable for any damages resulting from the use of this data.*

* = Most accurate load tested

** = Compressed load