


# CARTRIDGE

## 308 Norma Magnum - 200 grain

Version 8.0

# Nosler®

UP FRONT



## 308 Norma Magnum - 200 grain

## 30 Cal. (.308")

**MAXIMUM O.A.C.L. 3.347"**

**B.C. S.D.**

AccuBond®	200gr. Spitzer		0.588	0.301
Partition®	200gr. Spitzer		0.481	0.301
CASE TYPE:	Norma	PRIMER TYPE	Fed 215	
CASE HOLDS:	66.7 Gr. WATER	BARREL Length/Make	24" Wiseman	
		BARREL Twist	1-10"	

POWDER TYPE	POWDER CHG. GRS.	MUZZLE VEL. F.P.S.	LOAD DENSITY (VOLUME)
<b>IMR 4895</b>	54.0 * MAX.	2610	89%
	52.0	2550	86%
	50.0	2490	82%
<b>IMR 4320</b>	56.0 MAX.	2610	90%
	54.0	2550	87%
	52.0 *	2490	84%
<b>IMR 4350</b>	66.0 * MAX.	2740	** 105%
	64.0	2640	** 102%
	62.0	2540	98%
<b>Viht N165</b> Most Accurate Powder Tested	67.0 MAX.	2747	** 112%
	65.0	2678	** 108%
	63.0 *	2608	** 105%
<b>IMR 4831</b>	69.0 * MAX.	2760	** 110%
	67.0	2690	** 107%
	65.0	2620	** 104%
<b>H4831</b>	68.0 * MAX.	2820	** 106%
	66.0	2760	** 103%
	64.0	2690	100%
<b>RL22</b>	68.5 MAX.	2850	** 112%
	66.5	2768	** 108%
	64.5 *	2685	** 105%

All cartridge measurements are SAAMI maximum and due to variations from manufacturers actual measurements may vary  
 \* Because Nosler, Inc. has no control over the actual components selected, the manner in which they are assembled or the condition of the firearm used, no responsibility, either expressed or implied is assumed for the use of this data.  
 In no event shall Nosler, Inc. be liable for any damages resulting from the use of this data.

\* = Most accurate load tested

\*\* = Compressed load